

KEYBOARD-VIDEO-MOUSE SOLUTIONS

KVM CONSOLES



K-SA-171




K-SA-171-S1601P-E




K-SA-171-C1601P-E



K-SA-171-S801P-E



K-SA-171-C3201P-E



K-SA-171-CIP3201P-E

➤ **KVM** is a solution for secure access in server farms where simple, universal access is required.

DESCRIPTION

- Designed for deployment in server rooms or data centers, allowing either direct or remote access to individual servers (or their cascades). Console enables server configuration and administration from all main manufacturers (IBM, HP, DELL, SUN and others). Integrated KVM switch, LCD console (including keyboard and touch-pad) housed within a compact (1U high) design.
- Available in two types:
Sxxxx—DB15—direct cable
Cxxxx—Cat. 5—dongle via twisted pair cable

KVM SETS—LCD DRAWER & KVM SWITCH

Code ³	Number and type of ports	Access via IP	Description
K-SA-171-S801P-E	8× USB/PS2 ¹	–	up to 128 servers by 8-level cascade
K-SA-171-S1601P-E	16× USB/PS2 ¹	–	up to 128 servers by 8-level cascade
K-SA-171-C1601P-E	16× Cat. 5 ²	–	up to 128 servers by 8-level cascade
K-SA-171-C3201P-E	32× Cat. 5 ²	–	up to 128 servers by 8-level cascade
K-SA-171-CIP3201P-E	32× Cat. 5 ²	✓	up to 128 servers by 8-level cascade

¹ Includes 8 KVM cables (additional cables to be ordered separately).

² USB, PS/2 dongles or Cat. 5 cords required for use (to be ordered separately).

³ KVM set contains LCD type K-SA-171; can be replaced with any other LCD solution from LCD DRAWERS ONLY table.

LCD HOLDERS

➤ **LCD holders** include high-quality (17" and 19" diagonal) SAMSUNG monitors, allowing the screen to be folded when not in use, so that the total height of the console (including LCD monitor) does not exceed 1U. Includes extrusions designed for both easy assembly and drawing out the KVM/LCD console. CONTEG KVM/LCD holders come equipped with a full keyboard (104 keys, including numerical) and optional language localization, including a touchpad.

DESCRIPTION

- PS/2 or USB input into the LCD holder (according to the cabling terminal type)
- All LCD drawers include a standard English keyboard; other layouts available on request
- Optional language setting (USA, GBR, JPN, DEU, FRA, ITA, RUS, ESP, CHN, KOR, DNK, CHE, NOR and European localization)
- Equipped with a touchpad (with trackball option)
- Multilingual "on-screen" menu
- Sliding bars with fixed position to prevent movement during typing
- Easy connection to KVM console
- Standard power supply 230 V; 12, 24 and 48 V options available

LCD DRAWERS ONLY *

Code	H (in U)	LCD size	Dimensions (mm)			Dimensions including packing (mm)			Weight (kg)	
			W	D	H	W	D	H	Nett	Gross
K-SA-171	1	17"	442	650	44	589	856	168	16	22
K-SA-191	1	19"	442	650	44	589	856	168	17	23
K-LKD-171	1	17"	442	650	44	589	856	168	15	21

* LCD holders can be combined with individual KVM consoles from the CONTEG portfolio. Please don't hesitate to contact us if unable to locate the LCD holder or KVM console you desire. Special consoles and holders not included in standard offer.



CONTEG, spol. s r.o.

Stetkova 1638/18

140 00 Prague 4

Czech Republic

Tel.: +420 565 300 358

info@conteg.com

www.conteg.com

CONTEG